

Eaton UTGX1JC1492PY

In line receptacle, with cable gland backshell, for 12 male contacts, IP68/69K, keying Y; UTGX1JC1492PY

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX1JC1492PY
PRODUCT LENGTH/DEPTH	79 mm
PRODUCT HEIGHT	35.1 mm
PRODUCT WIDTH	35.1 mm
PRODUCT WEIGHT	32 g

**ENVIRONMENTAL
CONDITIONS**

Flammability rating UL94
V0
RoHS
REACH

BACKSHELL ANGLE

straight

BACKSHELL TYPE

Sealing Gland

**CONNECTOR ACCESSORY
OPTION**

Delivered with connector

**CONNECTOR
ORIENTATION**

Y

CONNECTOR TYPE

Receptacle

CONTACT DELIVERY

Not delivered

CONTACT GENDER

Pin (Male)

CONTACT TYPE

Crimp

COUPLING TYPE

1/3 Bayonet

LAYOUT

92

SHELL MATERIAL

Metal & Plastic

SHELL SIZE

14

MATING CYCLES

500

**OPERATING
TEMPERATURE - MAX**

105 °C

**OPERATING
TEMPERATURE - MIN**

-40 °C

RECEPTACLE TYPE

In-Line Receptacle

NUMBER OF CONTACTS

12

NUMBER OF CAVITY #16

12

SALT SPRAY

500 hour

3D[utgx1jc1492py.stp](#)**PROJECT NAME:****PROJECT NUMBER:****PREPARED BY:**

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

