

Eaton UTGX610E98PY

Plug, without backshell, with 6 male solder contacts, IP68/69K in unmated conditions, keying Y; UTGX610E98PY

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX610E98PY
PRODUCT LENGTH/DEPTH	24 mm
PRODUCT HEIGHT	26.2 mm
PRODUCT WIDTH	26.2 mm
PRODUCT WEIGHT	20 g

ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 V0
--------------------------	--

CONNECTOR ACCESSORY OPTION	No backshell possibility
----------------------------	--------------------------

CONNECTOR ORIENTATION	Y
-----------------------	---

CONNECTOR TYPE	Plug
----------------	------

CONTACT DELIVERY	Loaded
------------------	--------

CONTACT GENDER	Pin (Male)
----------------	------------

CONTACT TYPE	Solder Cup
--------------	------------

COUPLING TYPE	1/3 Bayonet
---------------	-------------

LAYOUT	E98
--------	-----

PLUG TYPE	Straight Plug
-----------	---------------

SHELL MATERIAL	Metal & Plastic
----------------	-----------------

SHELL SIZE	10
------------	----

MATING CYCLES	500
---------------	-----

OPERATING TEMPERATURE - MAX	105 °C
-----------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
-----------------------------	--------

NUMBER OF CONTACTS	6
--------------------	---

NUMBER OF CAVITY #20	3
----------------------	---

SALT SPRAY	500 hour
------------	----------

3D

[utgx610e98py.stp](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

