

Eaton UTGX612E8P

Plug, without backshell, with 8 male solder contacts, IP68/69K in unmated conditions; UTGX612E8P

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX612E8P
PRODUCT LENGTH/DEPTH	24 mm
PRODUCT HEIGHT	29.7 mm
PRODUCT WIDTH	29.7 mm
PRODUCT WEIGHT	22 g

**ENVIRONMENTAL
CONDITIONS**

Flammability rating UL94
V0
REACH
RoHS

**CONNECTOR ACCESSORY
OPTION**

No backshell possibility

**CONNECTOR
ORIENTATION**

N

CONNECTOR TYPE

Plug

CONTACT DELIVERY

Loaded

CONTACT GENDER

Pin (Male)

CONTACT TYPE

Solder Cup

COUPLING TYPE

1/3 Bayonet

LAYOUT

E8

PLUG TYPE

Straight Plug

SHELL MATERIAL

Metal & Plastic

SHELL SIZE

12

MATING CYCLES

500

**OPERATING
TEMPERATURE - MAX**

105 °C

**OPERATING
TEMPERATURE - MIN**

-40 °C

NUMBER OF CONTACTS

8

NUMBER OF CAVITY #16

8

SALT SPRAY

500 hour

3D

[utgx612e8p.stp](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

