

Eaton UTGX61419PY

Plug, without backshell, for 19 male contacts, IP68/69K, keying Y; UTGX61419PY

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX61419PY
PRODUCT LENGTH/DEPTH	25.5 mm
PRODUCT HEIGHT	34.6 mm
PRODUCT WIDTH	34.6 mm
PRODUCT WEIGHT	27 g

ENVIRONMENTAL CONDITIONS	RoHS REACH Flammability rating UL94 V0
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
LAYOUT	19
PLUG TYPE	Straight Plug
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	14
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	19
NUMBER OF CAVITY #20	19
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

