



□□□□□

Eaton UTGX61492P

Plug, without backshell, for 12 male contacts, IP68/69K; UTGX61492P

□□□□

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX61492P
PRODUCT LENGTH/DEPTH	25.5 mm
PRODUCT HEIGHT	34.6 mm
PRODUCT WIDTH	34.6 mm
PRODUCT WEIGHT	27 g



Powering Business Worldwide

0000	
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 REACH RoHS
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
LAYOUT	92
PLUG TYPE	Straight Plug
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	14
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	12
NUMBER OF CAVITY #16	12
SALT SPRAY	500 hour

00	
3D 00	utgx61492p.stp

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00: