



□□□□□

Eaton UTGX614E12SW

Plug, without backshell, with 12 female solder contacts, IP68/69K in unmated conditions, keying W; UTGX614E12SW

□□□□

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX614E12SW
PRODUCT LENGTH/DEPTH	24 mm
PRODUCT HEIGHT	34.6 mm
PRODUCT WIDTH	34.6 mm
PRODUCT WEIGHT	30 g

0000	
ENVIRONMENTAL CONDITIONS	RoHS REACH Flammability rating UL94 V0
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
LAYOUT	E12
PLUG TYPE	Straight Plug
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	14
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	12
NUMBER OF CAVITY #16	12
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:

00	utgx614e12sw.stp
3D 00	

