

Eaton UTGX6JC104S

Plug, with cable gland backshell, for 4 female contacts, IP68/69K; UTGX6JC104S

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX6JC104S
PRODUCT LENGTH/DEPTH	63.2 mm
PRODUCT HEIGHT	26.2 mm
PRODUCT WIDTH	26.2 mm
PRODUCT WEIGHT	28 g

**ENVIRONMENTAL
CONDITIONS**

RoHS
REACH
Flammability rating UL94
V0

BACKSHELL ANGLE

straight

BACKSHELL TYPE

Sealing Gland

**CONNECTOR ACCESSORY
OPTION**

Delivered with connector

**CONNECTOR
ORIENTATION**

N

CONNECTOR TYPE

Plug

CONTACT DELIVERY

Not delivered

CONTACT GENDER

Socket (Female)

CONTACT TYPE

Crimp

COUPLING TYPE

1/3 Bayonet

LAYOUT

4

PLUG TYPE

Straight Plug

SHELL MATERIAL

Metal & Plastic

SHELL SIZE

10

MATING CYCLES

500

**OPERATING
TEMPERATURE - MAX**

105 °C

**OPERATING
TEMPERATURE - MIN**

-40 °C

NUMBER OF CONTACTS

4

NUMBER OF CAVITY #16

4

SALT SPRAY

500 hour

3D[utgx6jc104s.stp](#)**PROJECT NAME:****PROJECT NUMBER:****PREPARED BY:**

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

