

Eaton UTGX6JC104SW

Plug, with cable gland backshell, for 4 female contacts, IP68/69K, keying W; UTGX6JC104SW

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX6JC104SW
PRODUCT LENGTH/DEPTH	63.2 mm
PRODUCT HEIGHT	26.2 mm
PRODUCT WIDTH	26.2 mm
PRODUCT WEIGHT	28 g

ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 V0 RoHS
--------------------------	--

BACKSHELL ANGLE	straight
-----------------	----------

BACKSHELL TYPE	Sealing Gland
----------------	---------------

CONNECTOR ACCESSORY OPTION	Delivered with connector
----------------------------	--------------------------

CONNECTOR ORIENTATION	W
-----------------------	---

CONNECTOR TYPE	Plug
----------------	------

CONTACT DELIVERY	Not delivered
------------------	---------------

CONTACT GENDER	Socket (Female)
----------------	-----------------

CONTACT TYPE	Crimp
--------------	-------

COUPLING TYPE	1/3 Bayonet
---------------	-------------

LAYOUT	4
--------	---

PLUG TYPE	Straight Plug
-----------	---------------

SHELL MATERIAL	Metal & Plastic
----------------	-----------------

SHELL SIZE	10
------------	----

MATING CYCLES	500
---------------	-----

OPERATING TEMPERATURE - MAX	105 °C
-----------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
-----------------------------	--------

NUMBER OF CONTACTS	4
--------------------	---

NUMBER OF CAVITY #16	4
----------------------	---

SALT SPRAY	500 hour
------------	----------

3D

[utgx6jc104sw.stp](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

