



□□□□□

Eaton UTGX6JC12E8SW

Plug, with cable gland backshell, with 8 female solder contacts, IP68/69K in unmated conditions, keying W; UTGX6JC12E8SW

□□□□

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX6JC12E8SW
PRODUCT LENGTH/DEPTH	66.7 mm
PRODUCT HEIGHT	29.7 mm
PRODUCT WIDTH	29.7 mm
PRODUCT WEIGHT	40 g

0000	
ENVIRONMENTAL CONDITIONS	REACH RoHS
BACKSHELL ANGLE	straight
BACKSHELL TYPE	Sealing Gland
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
LAYOUT	E8
PLUG TYPE	Straight Plug
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	12
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	8
NUMBER OF CAVITY #16	8
SALT SPRAY	500 hour

00	
3D 00	utgx6jc12e8sw.stp

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00: