

Eaton UTGX6JC14E19S

Plug, with cable gland backshell, with 19 female solder contacts, IP68/69K in unmated conditions; UTGX6JC14E19S

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX6JC14E19S
PRODUCT LENGTH/DEPTH	71.5 mm
PRODUCT HEIGHT	34.6 mm
PRODUCT WIDTH	34.6 mm
PRODUCT WEIGHT	52 g



Powering Business Worldwide

ENVIRONMENTAL CONDITIONS	REACH RoHS
BACKSHELL ANGLE	straight
BACKSHELL TYPE	Sealing Gland
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
LAYOUT	E19
PLUG TYPE	Straight Plug
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	14
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	19
NUMBER OF CAVITY #20	19
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
 30 Pembroke Road
 Dublin 4,
 Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

