

Eaton UTGX7106PW

Jam nut receptacle, without backshell, for 6 male contacts, IP68/69K, keying W; UTGX7106PW

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX7106PW
PRODUCT LENGTH/DEPTH	31.9 mm
PRODUCT HEIGHT	27 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	8 g

ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 V0 RoHS
--------------------------	--

CONNECTOR ACCESSORY OPTION	No backshell possibility
----------------------------	--------------------------

CONNECTOR ORIENTATION	W
-----------------------	---

CONNECTOR TYPE	Receptacle
----------------	------------

CONTACT DELIVERY	Not delivered
------------------	---------------

CONTACT GENDER	Pin (Male)
----------------	------------

CONTACT TYPE	Crimp
--------------	-------

COUPLING TYPE	1/3 Bayonet
---------------	-------------

LAYOUT	6
--------	---

SHELL MATERIAL	Metal & Plastic
----------------	-----------------

SHELL SIZE	10
------------	----

MATING CYCLES	500
---------------	-----

OPERATING TEMPERATURE - MAX	105 °C
-----------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
-----------------------------	--------

RECEPTACLE TYPE	Jam Nut Receptacle
-----------------	--------------------

NUMBER OF CONTACTS	6
--------------------	---

NUMBER OF CAVITY #20	6
----------------------	---

SALT SPRAY	500 hour
------------	----------

3D

[utgx7106pw.stp](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

