

Eaton UTGX712D14PW

Jam nut receptacle, without backshell, with 14 male PCB contacts, IP68/69K in unmated conditions, keying W; UTGX712D14PW

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX712D14PW
PRODUCT LENGTH/DEPTH	24.5 mm
PRODUCT HEIGHT	31.8 mm
PRODUCT WIDTH	31.8 mm
PRODUCT WEIGHT	14 g

ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 V0 RoHS
--------------------------	--

CONNECTOR ACCESSORY OPTION	No backshell possibility
----------------------------	--------------------------

CONNECTOR ORIENTATION	W
-----------------------	---

CONNECTOR TYPE	Receptacle
----------------	------------

CONTACT DELIVERY	Loaded
------------------	--------

CONTACT GENDER	Pin (Male)
----------------	------------

CONTACT TYPE	PCB
--------------	-----

COUPLING TYPE	1/3 Bayonet
---------------	-------------

LAYOUT	D14
--------	-----

SHELL MATERIAL	Metal & Plastic
----------------	-----------------

SHELL SIZE	12
------------	----

MATING CYCLES	500
---------------	-----

OPERATING TEMPERATURE - MAX	105 °C
-----------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
-----------------------------	--------

RECEPTACLE TYPE	Jam Nut Receptacle
-----------------	--------------------

NUMBER OF CONTACTS	14
--------------------	----

NUMBER OF CAVITY #20	14
----------------------	----

SALT SPRAY	500 hour
------------	----------

3D

[utgx712d14pw.stp](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

