

Eaton UTGX71419PX

Jam nut receptacle, without backshell, for 19 male contacts, IP68/69K, keying X; UTGX71419PX

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX71419PX
PRODUCT LENGTH/DEPTH	31.9 mm
PRODUCT HEIGHT	30.2 mm
PRODUCT WIDTH	30.2 mm
PRODUCT WEIGHT	14 g

**ENVIRONMENTAL
CONDITIONS**

Flammability rating UL94
V0
REACH
RoHS

**CONNECTOR ACCESSORY
OPTION**

No backshell possibility

**CONNECTOR
ORIENTATION**

X

CONNECTOR TYPE

Receptacle

CONTACT DELIVERY

Not delivered

CONTACT GENDER

Pin (Male)

CONTACT TYPE

Crimp

COUPLING TYPE

1/3 Bayonet

LAYOUT

19

SHELL MATERIAL

Metal & Plastic

SHELL SIZE

14

MATING CYCLES

500

**OPERATING
TEMPERATURE - MAX**

105 °C

**OPERATING
TEMPERATURE - MIN**

-40 °C

RECEPTACLE TYPE

Jam Nut Receptacle

NUMBER OF CONTACTS

19

NUMBER OF CAVITY #20

19

SALT SPRAY

500 hour

3D[utgx71419px.stp](#)**PROJECT NAME:****PROJECT NUMBER:****PREPARED BY:**

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

