

Eaton UTGX714D15SY32

Jam nut receptacle & hold down clips, without backshell, with 15 female PCB contacts, IP68/69K in unmated conditions, keying Y; UTGX714D15SY32

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX714D15SY32
PRODUCT LENGTH/DEPTH	24.5 mm
PRODUCT HEIGHT	30.2 mm
PRODUCT WIDTH	30.2 mm
PRODUCT WEIGHT	19 g

**ENVIRONMENTAL
CONDITIONS**

Flammability rating UL94
V0
REACH
RoHS

**CONNECTOR ACCESSORY
OPTION**

No backshell possibility

**CONNECTOR
ORIENTATION**

Y

CONNECTOR TYPE

Receptacle

CONTACT DELIVERY

Loaded

CONTACT GENDER

Socket (Female)

CONTACT TYPE

PCB

COUPLING TYPE

1/3 Bayonet

LAYOUT

D15

SHELL MATERIAL

Metal & Plastic

SHELL SIZE

14

MATING CYCLES

500

**OPERATING
TEMPERATURE - MAX**

105 °C

**OPERATING
TEMPERATURE - MIN**

-40 °C

RECEPTACLE TYPE

Jam Nut Receptacle

NUMBER OF CONTACTS

15

SALT SPRAY

500 hour

3D

[utgx714d15sy32.stp](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

