



□□□□□

Eaton UTGX714D19SW

Jam nut receptacle, without backshell, with 19 female PCB contacts, IP68/69K in unmated conditions, keying W; UTGX714D19SW

□□□□

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX714D19SW
PRODUCT LENGTH/DEPTH	24.5 mm
PRODUCT HEIGHT	30.2 mm
PRODUCT WIDTH	30.2 mm
PRODUCT WEIGHT	18 g



Powering Business Worldwide

0000	
ENVIRONMENTAL CONDITIONS	RoHS REACH Flammability rating UL94 V0
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
LAYOUT	D19
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	14
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	19
NUMBER OF CAVITY #20	19
SALT SPRAY	500 hour

00	
3D 00	utgx714d19sw.stp

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00: