

Eaton

UTL1103G1S16AWG

Evaluation kit, with female in line receptacle and contacts, 3G1 layout;
UTL1103G1S16AWG

PRODUCT NAME	Eaton Souriau UTL series uL/IEC power and control supply
CATALOG NUMBER	UTL1103G1S16AWG
PRODUCT LENGTH/DEPTH	28.6 mm
PRODUCT HEIGHT	28.6 mm
PRODUCT WIDTH	28.6 mm
PRODUCT WEIGHT	14.3 g
COMPLIANCES	IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details)

CURRENT RATING	16 A IEC 16 A UL
FITTED WITH:	First mate last break capability Layout with ground cavity
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 REACH RoHS
ENVIRONMENTAL RESISTANCE	Resistant against gasoline Resistant against basic bath Resistant against oil Resistant against acid bath Resistant against mineral oil UV resistant, no degradation after 5 years of exposure in natural environment
TEST CURRENT	16 A UL16 A IEC
TEST VOLTAGE	600 V UL 500 V IEC
CONNECTOR ACCESSORY OPTION	Only to be overmolded
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	3G1
SHELL MATERIAL	Plastic
SHELL SIZE	10
MATING CYCLES	1000
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	In-Line Receptacle
NUMBER OF CONTACTS	4
NUMBER OF CAVITY #16	4
SALT SPRAY	1000 hour



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

