

# Eaton UTL6103G1P03

Male plug grey, 3G1 layout; UTL6103G1P03

PRODUCT NAME	Eaton Souriau UTL series uL/IEC power and control supply
CATALOG NUMBER	UTL6103G1P03
PRODUCT LENGTH/DEPTH	24 mm
PRODUCT HEIGHT	24 mm
PRODUCT WIDTH	24 mm
PRODUCT WEIGHT	10 g
COMPLIANCES	UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details)

CURRENT RATING	16 A IEC 16 A UL
FITTED WITH:	Layout with ground cavity First mate last break capability
ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 V0 RoHS
ENVIRONMENTAL RESISTANCE	Resistant against gasoline Resistant against oil Resistant against basic bath Resistant against acid bath  Resistant against mineral oil UV resistant, no degradation after 5 years of exposure in natural environment
TEST CURRENT	16 A UL16 A IEC
TEST VOLTAGE	500 V IEC 600 V UL
CONNECTOR ACCESSORY OPTION	Only to be overmolded
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	3G1
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic
SHELL SIZE	10
MATING CYCLES	1000
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	4
NUMBER OF CAVITY #16	4
SALT SPRAY	1000 hour



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

