

# Eaton

## UTL6103G1P14AWG

Evaluation kit, with male plug and contacts,  
3G1 layout; UTL6103G1P14AWG

PRODUCT NAME	Eaton Souriau UTL series uL/IEC power and control supply
CATALOG NUMBER	UTL6103G1P14AWG
PRODUCT LENGTH/DEPTH	24 mm
PRODUCT HEIGHT	24 mm
PRODUCT WIDTH	24 mm
PRODUCT WEIGHT	10 g
COMPLIANCES	IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details)

<b>CURRENT RATING</b>	16 A UL 16 A IEC
<b>FITTED WITH:</b>	Layout with ground cavity First mate last break capability
<b>ENVIRONMENTAL CONDITIONS</b>	REACH RoHS Flammability rating UL94 V0
<b>ENVIRONMENTAL RESISTANCE</b>	Resistant against mineral oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against basic bath Resistant against oil Resistant against gasoline Resistant against acid bath
<b>TEST CURRENT</b>	16 A UL16 A IEC
<b>TEST VOLTAGE</b>	500 V IEC 600 V UL
<b>CONNECTOR ACCESSORY OPTION</b>	Only to be overmolded
<b>CONNECTOR TYPE</b>	Plug
<b>CONTACT DELIVERY</b>	Unloaded
<b>CONTACT GENDER</b>	Pin (Male)
<b>CONTACT TYPE</b>	Crimp
<b>COUPLING TYPE</b>	Push-Pull
<b>DEGREE OF PROTECTION</b>	IP68
<b>INSERT MATERIAL</b>	Polyamide
<b>LAYOUT</b>	3G1
<b>PLUG TYPE</b>	Straight Plug
<b>SHELL MATERIAL</b>	Plastic
<b>SHELL SIZE</b>	10
<b>MATING CYCLES</b>	1000
<b>OPERATING TEMPERATURE - MAX</b>	105 °C
<b>OPERATING TEMPERATURE - MIN</b>	-40 °C
<b>NUMBER OF CONTACTS</b>	4
<b>NUMBER OF CAVITY #16</b>	4
<b>SALT SPRAY</b>	1000 hour



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

