



Eaton UTS010D98SZ

Plastic square flange receptacle, without backshell, with 6 female PCB contacts, IP68/69K in unmated conditions, keying Z; UTS010D98SZ

□□□□

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS010D98SZ
PRODUCT LENGTH/DEPTH	21.5 mm
PRODUCT HEIGHT	23.8 mm
PRODUCT WIDTH	23.8 mm
PRODUCT WEIGHT	7.8 g
COMPLIANCES	UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) ROHS exemption 6.c

□□□□

□□

CURRENT RATING	7 A IEC 6 A UL
ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 HB
ENVIRONMENTAL RESISTANCE	Resistant against gasoline UV resistant, no degradation after 5 years of exposure in natural environment Resistant against mineral oil Resistant against oil Resistant against basic bath Resistant against acid bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz
TEST CURRENT	7 A IEC 6 A UL 6 A CSA
TEST VOLTAGE	250 V UL 50 V IEC 250 V CSA
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	Z
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	98
SHELL MATERIAL	Plastic
SHELL SIZE	10
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	6

NUMBER OF CAVITY #20	6
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

