

Eaton UTS012D10S

Plastic square flange receptacle, without backshell, with 10 female PCB contacts, IP68/69K in unmated conditions; UTS012D10S

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS012D10S
PRODUCT LENGTH/DEPTH	21.5 mm
PRODUCT HEIGHT	26.2 mm
PRODUCT WIDTH	26.2 mm
PRODUCT WEIGHT	12 g
COMPLIANCES	CSA-C22.2 No.182.3 (please contact us for more details) ROHS exemption 6.c IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details)

CURRENT RATING	10 A UL 16 A IEC
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 HB REACH RoHS
ENVIRONMENTAL RESISTANCE	Resistant against mineral oil Resistant against basic bath Resistant against oil UV resistant, no degradation after 5 years of exposure in natural environment Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against acid bath Resistant against gasoline
TEST CURRENT	10 A UL 16 A IEC 7 A CSA
TEST VOLTAGE	500 V CSA 500 V UL 300 V IEC
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	10
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	10
NUMBER OF CAVITY #20	10
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

