

Eaton UTS012E3S

Plastic square flange receptacle, without backshell, with 3 female solder contacts, IP68/69K in unmated conditions; UTS012E3S

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS012E3S
PRODUCT LENGTH/DEPTH	21.5 mm
PRODUCT HEIGHT	26.2 mm
PRODUCT WIDTH	26.2 mm
PRODUCT WEIGHT	10.2 g
COMPLIANCES	UL 1977 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) ROHS exemption 6.c IEC 61984 (please contact us for more details)

CURRENT RATING	16 A IEC 13 A UL
ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 HB
ENVIRONMENTAL RESISTANCE	Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against oil Resistant against gasoline Resistant against mineral oil Resistant against basic bath Resistant against acid bath UV resistant, no degradation after 5 years of exposure in natural environment
TEST CURRENT	16 A IEC 13 A UL 13 A CSA
TEST VOLTAGE	150 V IEC 600 V CSA 600 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	3
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	3
NUMBER OF CAVITY #16	3
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

