

Eaton UTS014D12P

Plastic square flange receptacle, without backshell, with 12 male PCB contacts, IP68/69K in unmated conditions; UTS014D12P

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS014D12P
PRODUCT LENGTH/DEPTH	21.5 mm
PRODUCT HEIGHT	28.6 mm
PRODUCT WIDTH	28.6 mm
PRODUCT WEIGHT	16.6 g
COMPLIANCES	UL 1977 (please contact us for more details) ROHS exemption 6.c IEC 61984 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details)



CURRENT RATING	4 A IEC 4.5 A UL
ENVIRONMENTAL CONDITIONS	RoHS Flammability rating UL94 HB REACH
ENVIRONMENTAL RESISTANCE	Resistant against mineral oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against acid bath Resistant against basic bath Resistant against oil Resistant against gasoline Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz
TEST CURRENT	4 A IEC 4.5 A CSA 4.5 A UL
TEST VOLTAGE	250 V CSA 250 V UL 50 V IEC
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	12
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	12
NUMBER OF CAVITY #16	4
NUMBER OF CAVITY #20	8
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

