

## Eaton UTS014D15SW

Plastic square flange receptacle, without backshell, with 15 female PCB contacts, IP68/69K in unmated conditions, keying W; UTS014D15SW

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS014D15SW
<b>PRODUCT LENGTH/DEPTH</b>	21.5 mm
<b>PRODUCT HEIGHT</b>	28.6 mm
<b>PRODUCT WIDTH</b>	28.6 mm
<b>PRODUCT WEIGHT</b>	20.6 g
<b>COMPLIANCES</b>	UL 1977 (please contact us for more details) ROHS exemption 6.c IEC 61984 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details)

CURRENT RATING	12 A UL 4 A IEC
ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 HB RoHS
ENVIRONMENTAL RESISTANCE	Resistant against basic bath Resistant against gasoline Resistant against mineral oil UV resistant, no degradation after 5 years of exposure in natural environment Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against acid bath  Resistant against oil
TEST CURRENT	12 A CSA 4 A IEC 12 A UL
TEST VOLTAGE	600 V UL 50 V IEC 600 V CSA
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	15
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	15
NUMBER OF CAVITY #16	1
NUMBER OF CAVITY #20	14
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

