

Eaton UTS014D5SX

Plastic square flange receptacle, without backshell, with 5 female PCB contacts, IP68/69K in unmated conditions, keying X; UTS014D5SX

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS014D5SX
PRODUCT LENGTH/DEPTH	21.5 mm
PRODUCT HEIGHT	28.6 mm
PRODUCT WIDTH	28.6 mm
PRODUCT WEIGHT	16.7 g
COMPLIANCES	CSA-C22.2 No.182.3 (please contact us for more details) ROHS exemption 6.c IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details)

CURRENT RATING	16 A IEC 12 A UL
ENVIRONMENTAL CONDITIONS	RoHS REACH Flammability rating UL94 HB
ENVIRONMENTAL RESISTANCE	Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against gasoline Resistant against acid bath Resistant against basic bath Resistant against mineral oil
TEST CURRENT	12 A UL 12 A CSA 16 A IEC
TEST VOLTAGE	150 V IEC 600 V CSA 600 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	X
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	5
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	5
NUMBER OF CAVITY #16	5
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

