

Eaton UTS014E18PZ

Plastic square flange receptacle, without backshell, with 18 male solder contacts, IP68/69K in unmated conditions, keying Z; UTS014E18PZ

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS014E18PZ
PRODUCT LENGTH/DEPTH	21.5 mm
PRODUCT HEIGHT	28.6 mm
PRODUCT WIDTH	28.6 mm
PRODUCT WEIGHT	15.5 g
COMPLIANCES	CSA-C22.2 No.182.3 (please contact us for more details) UL 1977 (please contact us for more details) ROHS exemption 6.c IEC 61984 (please contact us for more details)



CURRENT RATING	4 A UL 5 A IEC
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 HB REACH RoHS
ENVIRONMENTAL RESISTANCE	UV resistant, no degradation after 5 years of exposure in natural environment Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against oil Resistant against acid bath Resistant against gasoline Resistant against mineral oil
TEST CURRENT	4 A CSA 5 A IEC 4 A UL
TEST VOLTAGE	250 V CSA 250 V UL 50 V IEC
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	Z
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	18
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	18
NUMBER OF CAVITY #20	18
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

