

# Eaton UTS014E19P

Plastic square flange receptacle, without backshell, with 19 male solder contacts, IP68/69K in unmated conditions; UTS014E19P

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS014E19P
<b>PRODUCT LENGTH/DEPTH</b>	21.5 mm
<b>PRODUCT HEIGHT</b>	28.6 mm
<b>PRODUCT WIDTH</b>	28.6 mm
<b>PRODUCT WEIGHT</b>	14.5 g
<b>COMPLIANCES</b>	IEC 61984 (please contact us for more details) ROHS exemption 6.c UL 1977 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details)



Powering Business Worldwide

<b>CURRENT RATING</b>	5 A IEC 4 A UL
<b>ENVIRONMENTAL CONDITIONS</b>	RoHS Flammability rating UL94 HB REACH
<b>ENVIRONMENTAL RESISTANCE</b>	Resistant against gasoline Resistant against basic bath Resistant against acid bath  Resistant against oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against mineral oil Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz
<b>TEST CURRENT</b>	4 A CSA 4 A UL 5 A IEC
<b>TEST VOLTAGE</b>	250 V CSA 250 V UL 32 V IEC
<b>CONNECTOR ACCESSORY OPTION</b>	No backshell possibility
<b>CONNECTOR ORIENTATION</b>	N
<b>CONNECTOR TYPE</b>	Receptacle
<b>CONTACT DELIVERY</b>	Loaded
<b>CONTACT GENDER</b>	Pin (Male)
<b>CONTACT PLATING</b>	Gold
<b>CONTACT TYPE</b>	Solder Cup
<b>COUPLING TYPE</b>	1/3 Bayonet
<b>DEGREE OF PROTECTION</b>	IP68
<b>INSERT MATERIAL</b>	Neoprene
<b>LAYOUT</b>	19
<b>SHELL MATERIAL</b>	Plastic
<b>SHELL SIZE</b>	14
<b>MATING CYCLES</b>	250
<b>OPERATING TEMPERATURE - MAX</b>	105 °C
<b>OPERATING TEMPERATURE - MIN</b>	-40 °C



<b>RECEPTACLE TYPE</b>	Square Flange Receptacle
<b>NUMBER OF CONTACTS</b>	19
<b>NUMBER OF CAVITY #20</b>	19
<b>SALT SPRAY</b>	500 hour

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

