

Eaton UTS014E5PW

Plastic square flange receptacle, without backshell, with 5 male solder contacts, IP68/69K in unmated conditions, keying W; UTS014E5PW

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS014E5PW
PRODUCT LENGTH/DEPTH	21.5 mm
PRODUCT HEIGHT	28.6 mm
PRODUCT WIDTH	28.6 mm
PRODUCT WEIGHT	11.9 g
COMPLIANCES	IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) ROHS exemption 6.c

CURRENT RATING	16 A IEC 12 A UL
ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 HB
ENVIRONMENTAL RESISTANCE	UV resistant, no degradation after 5 years of exposure in natural environment Resistant against basic bath Resistant against acid bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against gasoline Resistant against mineral oil Resistant against oil
TEST CURRENT	12 A CSA 12 A UL 16 A IEC
TEST VOLTAGE	600 V UL 150 V IEC 600 V CSA
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	5
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C

RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	5
NUMBER OF CAVITY #16	5
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

