

Eaton UTS018E32P

Plastic square flange receptacle, without backshell, with 32 male solder contacts, IP68/69K in unmated conditions; UTS018E32P

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS018E32P
PRODUCT LENGTH/DEPTH	21.5 mm
PRODUCT HEIGHT	33.3 mm
PRODUCT WIDTH	33.3 mm
PRODUCT WEIGHT	24 g
COMPLIANCES	IEC 61984 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) ROHS exemption 6.c UL 1977 (please contact us for more details)

CURRENT RATING	4 A IEC 5 A UL
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 HB REACH RoHS
ENVIRONMENTAL RESISTANCE	Resistant against gasoline Resistant against acid bath
	Resistant against oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against basic bath Resistant against mineral oil Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz
TEST CURRENT	4 A CSA 4 A IEC 5 A UL
TEST VOLTAGE	32 V IEC 250 V CSA 250 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	32
SHELL MATERIAL	Plastic
SHELL SIZE	18
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	32
NUMBER OF CAVITY #20	32
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

