



Eaton UTS1JC1492PW

Plastic in line receptacle, with cable gland backshell, for 12 male contacts, IP68/69K, keying W; UTS1JC1492PW

□□□□

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS1JC1492PW
PRODUCT LENGTH/DEPTH	78.5 mm
PRODUCT HEIGHT	35.1 mm
PRODUCT WIDTH	35.1 mm
PRODUCT WEIGHT	42.6 g
COMPLIANCES	UL 1977 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details)

□□□□

□□

CURRENT RATING	10 A IEC 10 A UL
ENVIRONMENTAL CONDITIONS	Fire and smoke rating I2F3 according to NFF 16101 and NFF 16102 RoHS REACH Flammability rating UL94 V0 Fire & Smoke
ENVIRONMENTAL RESISTANCE	Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against acid bath Resistant against mineral oil Resistant against oil Resistant against basic bath Resistant against gasoline UV resistant, no degradation after 5 years of exposure in natural environment
TEST CURRENT	10 A IEC 7 A CSA 10 A UL
TEST VOLTAGE	600 V CSA 63 V IEC 600 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Sealing Gland
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	92
SHELL MATERIAL	Plastic
SHELL SIZE	14
CABLE DIAMETER - MAX	14 mm
CABLE DIAMETER - MIN	5 mm

MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	In-Line Receptacle
NUMBER OF CONTACTS	12
NUMBER OF CAVITY #16	12
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4, Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

