

Eaton UTS6128PW

Plastic plug, without backshell, for 8 male contacts, IP68/69K, keying W; UTS6128PW

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS6128PW
PRODUCT LENGTH/DEPTH	33 mm
PRODUCT HEIGHT	29.7 mm
PRODUCT WIDTH	29.7 mm
PRODUCT WEIGHT	18.6 g
COMPLIANCES	CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details)

CURRENT RATING	10 A IEC 10 A UL
FITTED WITH:	First mate last break capability(optional) Last mate first break capability(optional)
ENVIRONMENTAL CONDITIONS	REACH RoHS Fire and smoke rating I2F3 according to NFF 16101 and NFF 16102 Fire & Smoke Flammability rating UL94 V0
ENVIRONMENTAL RESISTANCE	Resistant against mineral oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against acid bath Resistant against gasoline Resistant against oil
TEST CURRENT	10 A UL 7 A CSA 10 A IEC
TEST VOLTAGE	500 V CSA 500 V UL 80 V IEC
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic



SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	8
NUMBER OF CAVITY #16	8
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

