

Eaton UTS61492PY

Plastic plug, without backshell, for 12 male contacts, IP68/69K, keying Y; UTS61492PY

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS61492PY
PRODUCT LENGTH/DEPTH	33 mm
PRODUCT HEIGHT	34.4 mm
PRODUCT WIDTH	34.6 mm
PRODUCT WEIGHT	17.9 g
COMPLIANCES	CSA-C22.2 No.182.3 (please contact us for more details) UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details)



CURRENT RATING	10 A IEC 10 A UL
ENVIRONMENTAL CONDITIONS	Fire and smoke rating I2F3 according to NFF 16101 and NFF 16102 Flammability rating UL94 V0 Fire & Smoke REACH RoHS
ENVIRONMENTAL RESISTANCE	Resistant against mineral oil UV resistant, no degradation after 5 years of exposure in natural environment Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against gasoline Resistant against acid bath Resistant against oil Resistant against basic bath
TEST CURRENT	10 A IEC 10 A UL 7 A CSA
TEST VOLTAGE	600 V UL 600 V CSA 63 V IEC
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	92
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250

OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	12
NUMBER OF CAVITY #16	12
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

