

# Eaton UTS61832SX

Plastic plug, without backshell, for 32 female contacts, IP68/69K, keying X; UTS61832SX

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS61832SX
<b>PRODUCT LENGTH/DEPTH</b>	37 mm
<b>PRODUCT HEIGHT</b>	41.3 mm
<b>PRODUCT WIDTH</b>	41.3 mm
<b>PRODUCT WEIGHT</b>	26.6 g
<b>COMPLIANCES</b>	IEC 61984 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) UL 1977 (please contact us for more details)



CURRENT RATING	5 A UL 4 A IEC
ENVIRONMENTAL CONDITIONS	Fire & Smoke Fire and smoke rating I2F3 according to NFF 16101 and NFF 16102 Flammability rating UL94 V0 RoHS REACH
ENVIRONMENTAL RESISTANCE	Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz UV resistant, no degradation after 5 years of exposure in natural environment Resistant against acid bath  Resistant against gasoline Resistant against oil Resistant against mineral oil Resistant against basic bath
TEST CURRENT	4 A CSA 4 A IEC 5 A UL
TEST VOLTAGE	250 V CSA 250 V UL 32 V IEC
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	X
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	32
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic
SHELL SIZE	18
MATING CYCLES	250

<b>OPERATING TEMPERATURE - MAX</b>	105 °C
<b>OPERATING TEMPERATURE - MIN</b>	-40 °C
<b>NUMBER OF CONTACTS</b>	32
<b>NUMBER OF CAVITY #20</b>	32
<b>SALT SPRAY</b>	500 hour

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
  
© 2025

Follow us on social media to get the latest product and support information.

