

Eaton UTS6FC1210PW

Plastic plug, with conduit adapter, for 10 male contacts, IP68/69K, keying W;
UTS6FC1210PW

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS6FC1210PW
PRODUCT LENGTH/DEPTH	61 mm
PRODUCT HEIGHT	29.7 mm
PRODUCT WIDTH	29.7 mm
PRODUCT WEIGHT	28.45 g
COMPLIANCES	IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details)



CURRENT RATING	6 A IEC 5 A UL
ENVIRONMENTAL CONDITIONS	Fire and smoke rating I2F3 according to NFF 16101 and NFF 16102 RoHS Fire & Smoke Flammability rating UL94 V0 REACH
ENVIRONMENTAL RESISTANCE	Resistant against gasoline Resistant against oil Resistant against mineral oil Resistant against acid bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against basic bath UV resistant, no degradation after 5 years of exposure in natural environment
TEST CURRENT	4 A CSA 6 A IEC 5 A UL
TEST VOLTAGE	250 V CSA 250 V UL 50 V IEC
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	For Flexible Conduit
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	10
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic

SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	10
NUMBER OF CAVITY #20	10
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

