

# Eaton UTS6FC1210PX

Plastic plug, with conduit adapter, for 10 male contacts, IP68/69K, keying X; UTS6FC1210PX

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS6FC1210PX
<b>PRODUCT LENGTH/DEPTH</b>	61 mm
<b>PRODUCT HEIGHT</b>	29.7 mm
<b>PRODUCT WIDTH</b>	29.7 mm
<b>PRODUCT WEIGHT</b>	28.45 g
<b>COMPLIANCES</b>	UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details)



CURRENT RATING	6 A IEC 5 A UL
ENVIRONMENTAL CONDITIONS	REACH Fire and smoke rating I2F3 according to NFF 16101 and NFF 16102 Fire & Smoke Flammability rating UL94 V0 RoHS
ENVIRONMENTAL RESISTANCE	Resistant against gasoline UV resistant, no degradation after 5 years of exposure in natural environment Resistant against mineral oil Resistant against oil Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against acid bath
TEST CURRENT	4 A CSA 6 A IEC 5 A UL
TEST VOLTAGE	250 V CSA 250 V UL 50 V IEC
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	For Flexible Conduit
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	X
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	10
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic
SHELL SIZE	12

MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	10
NUMBER OF CAVITY #20	10
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

