

Eaton UTS6FC128P

Plastic plug, with conduit adapter, for 8 male contacts, IP68/69K; UTS6FC128P

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS6FC128P
PRODUCT LENGTH/DEPTH	61 mm
PRODUCT HEIGHT	29.7 mm
PRODUCT WIDTH	29.7 mm
PRODUCT WEIGHT	27.47 g
COMPLIANCES	CSA-C22.2 No.182.3 (please contact us for more details) UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details)

CURRENT RATING	10 A IEC 10 A UL
FITTED WITH:	First mate last break capability(optional) Last mate first break capability(optional)
ENVIRONMENTAL CONDITIONS	Fire and smoke rating I2F3 according to NFF 16101 and NFF 16102 Fire & Smoke REACH Flammability rating UL94 V0 RoHS
ENVIRONMENTAL RESISTANCE	Resistant against gasoline Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against mineral oil Resistant against acid bath Resistant against oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against basic bath
TEST CURRENT	7 A CSA 10 A IEC 10 A UL
TEST VOLTAGE	500 V UL 80 V IEC 500 V CSA
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	For Flexible Conduit
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide



PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	8
NUMBER OF CAVITY #16	8
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

