

## Eaton UTS6FC12E10PZ

Plastic plug, with conduit adapter, with 10 male solder contacts, IP68/69K in unmated conditions, keying Z; UTS6FC12E10PZ

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS6FC12E10PZ
<b>PRODUCT LENGTH/DEPTH</b>	61 mm
<b>PRODUCT HEIGHT</b>	29.7 mm
<b>PRODUCT WIDTH</b>	29.7 mm
<b>PRODUCT WEIGHT</b>	24.7 g
<b>COMPLIANCES</b>	ROHS exemption 6.c UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details)

CURRENT RATING	10 A UL 16 A IEC
ENVIRONMENTAL CONDITIONS	RoHS Flammability rating UL94 HB REACH
ENVIRONMENTAL RESISTANCE	UV resistant, no degradation after 5 years of exposure in natural environment Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against acid bath  Resistant against mineral oil Resistant against basic bath Resistant against gasoline Resistant against oil
TEST CURRENT	16 A IEC 10 A UL 7 A CSA
TEST VOLTAGE	500 V UL 300 V IEC 500 V CSA
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	For Flexible Conduit
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	Z
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	10
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250



<b>OPERATING TEMPERATURE - MAX</b>	105 °C
<b>OPERATING TEMPERATURE - MIN</b>	-40 °C
<b>NUMBER OF CONTACTS</b>	10
<b>NUMBER OF CAVITY #20</b>	10
<b>SALT SPRAY</b>	500 hour

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

