



## Eaton UTS6FC12E10SZ

Plastic plug, with conduit adapter, with 10 female solder contacts, IP68/69K in unmated conditions, keying Z; UTS6FC12E10SZ

□□□□

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS6FC12E10SZ
<b>PRODUCT LENGTH/DEPTH</b>	61 mm
<b>PRODUCT HEIGHT</b>	29.7 mm
<b>PRODUCT WIDTH</b>	29.7 mm
<b>PRODUCT WEIGHT</b>	26.1 g
<b>COMPLIANCES</b>	CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details) ROHS exemption 6.c UL 1977 (please contact us for more details)

□□□□

□□

<b>CURRENT RATING</b>	10 A UL 16 A IEC
<b>ENVIRONMENTAL CONDITIONS</b>	Flammability rating UL94 HB REACH RoHS
<b>ENVIRONMENTAL RESISTANCE</b>	Resistant against oil Resistant against gasoline Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against basic bath Resistant against mineral oil Resistant against acid bath  UV resistant, no degradation after 5 years of exposure in natural environment
<b>TEST CURRENT</b>	10 A UL 16 A IEC 7 A CSA
<b>TEST VOLTAGE</b>	500 V CSA 300 V IEC 500 V UL
<b>BACKSHELL ANGLE</b>	Straight
<b>BACKSHELL TYPE</b>	For Flexible Conduit
<b>CONNECTOR ACCESSORY OPTION</b>	Delivered with connector
<b>CONNECTOR ORIENTATION</b>	Z
<b>CONNECTOR TYPE</b>	Plug
<b>CONTACT DELIVERY</b>	Loaded
<b>CONTACT GENDER</b>	Socket (Female)
<b>CONTACT PLATING</b>	Gold
<b>CONTACT TYPE</b>	Solder Cup
<b>COUPLING TYPE</b>	1/3 Bayonet
<b>DEGREE OF PROTECTION</b>	IP68
<b>INSERT MATERIAL</b>	Neoprene
<b>LAYOUT</b>	10
<b>PLUG TYPE</b>	Straight Plug
<b>SHELL MATERIAL</b>	Plastic
<b>SHELL SIZE</b>	12
<b>MATING CYCLES</b>	250
<b>OPERATING TEMPERATURE - MAX</b>	105 °C

OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	10
NUMBER OF CAVITY #20	10
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,  Eaton.com

© 2025  

Follow us on social media to get the latest product and support information.

