

## Eaton UTS6FC12E8P

Plastic plug, with conduit adapter, with 8 male solder contacts, IP68/69K in unmated conditions; UTS6FC12E8P

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS6FC12E8P
<b>PRODUCT LENGTH/DEPTH</b>	61 mm
<b>PRODUCT HEIGHT</b>	29.7 mm
<b>PRODUCT WIDTH</b>	29.7 mm
<b>PRODUCT WEIGHT</b>	24.1 g
<b>COMPLIANCES</b>	CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details) ROHS exemption 6.c

CURRENT RATING	4.5 A UL 6 A IEC
ENVIRONMENTAL CONDITIONS	RoHS REACH Flammability rating UL94 HB
ENVIRONMENTAL RESISTANCE	Resistant against basic bath UV resistant, no degradation after 5 years of exposure in natural environment Resistant against acid bath  Resistant against oil Resistant against mineral oil Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against gasoline
TEST CURRENT	4.5 A UL 6 A IEC 4.5 A CSA
TEST VOLTAGE	250 V UL 32 V IEC 250 V CSA
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	For Flexible Conduit
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250
OPERATING	105 °C



TEMPERATURE - MAX	
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	8
NUMBER OF CAVITY #16	8
NUMBER OF CAVITY #20	8
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

