

# Eaton UTS6FC1419S

Plastic plug, with conduit adapter, for 19 female contacts, IP68/69K; UTS6FC1419S

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS6FC1419S
<b>PRODUCT LENGTH/DEPTH</b>	61 mm
<b>PRODUCT HEIGHT</b>	34.4 mm
<b>PRODUCT WIDTH</b>	34.6 mm
<b>PRODUCT WEIGHT</b>	33.34 g
<b>COMPLIANCES</b>	UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details)



CURRENT RATING	5 A IEC 5 A UL
ENVIRONMENTAL CONDITIONS	REACH Fire and smoke rating I2F3 according to NFF 16101 and NFF 16102 RoHS Fire & Smoke Flammability rating UL94 V0
ENVIRONMENTAL RESISTANCE	Resistant against basic bath Resistant against mineral oil Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against acid bath  Resistant against gasoline Resistant against oil UV resistant, no degradation after 5 years of exposure in natural environment
TEST CURRENT	5 A IEC 5 A UL 4 A CSA
TEST VOLTAGE	250 V UL 32 V IEC 250 V CSA
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	For Flexible Conduit
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	19
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic

SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	19
NUMBER OF CAVITY #20	19
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

