

Eaton UTS6FC14E19S

Plastic plug, with conduit adapter, with 19 female solder contacts, IP68/69K in unmated conditions; UTS6FC14E19S

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS6FC14E19S
PRODUCT LENGTH/DEPTH	61 mm
PRODUCT HEIGHT	34.4 mm
PRODUCT WIDTH	34.6 mm
PRODUCT WEIGHT	35.64 g
COMPLIANCES	UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details) ROHS exemption 6.c CSA-C22.2 No.182.3 (please contact us for more details)

CURRENT RATING	5 A IEC 4 A UL
ENVIRONMENTAL CONDITIONS	RoHS Flammability rating UL94 HB REACH
ENVIRONMENTAL RESISTANCE	Resistant against oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against gasoline Resistant against mineral oil Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against basic bath Resistant against acid bath
TEST CURRENT	5 A IEC 4 A CSA 4 A UL
TEST VOLTAGE	32 V IEC 250 V UL 250 V CSA
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	For Flexible Conduit
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	19
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING	105 °C



TEMPERATURE - MAX	
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	19
NUMBER OF CAVITY #20	19
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
 30 Pembroke Road
 Dublin 4,
 Eaton.com
 © 2025

Follow us on social media to get the latest product and support information.

