

Eaton UTS6FC1832SW

Plastic plug, with conduit adapter, for 32 female contacts, IP68/69K, keying W; UTS6FC1832SW

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS6FC1832SW
PRODUCT LENGTH/DEPTH	61.1 mm
PRODUCT HEIGHT	41.3 mm
PRODUCT WIDTH	41.3 mm
PRODUCT WEIGHT	56 g
COMPLIANCES	CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details)

CURRENT RATING	4 A IEC 5 A UL
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 Fire and smoke rating I2F3 according to NFF 16101 and NFF 16102 Fire & Smoke REACH RoHS
ENVIRONMENTAL RESISTANCE	Resistant against gasoline Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz UV resistant, no degradation after 5 years of exposure in natural environment Resistant against mineral oil Resistant against acid bath Resistant against oil
TEST CURRENT	4 A CSA 4 A IEC 5 A UL
TEST VOLTAGE	250 V CSA 32 V IEC 250 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	For Flexible Conduit
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	32
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic



SHELL SIZE	18
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	32
NUMBER OF CAVITY #20	32
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

