



Eaton UTS6GJC1492SY

Plastic plug, with cable gland and grommet backshell, for 12 female contacts, IP68/69K, keying Y; UTS6GJC1492SY

□□□□

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS6GJC1492SY
PRODUCT LENGTH/DEPTH	70 mm
PRODUCT HEIGHT	34.4 mm
PRODUCT WIDTH	34.6 mm
PRODUCT WEIGHT	42.8 g
COMPLIANCES	UL 1977 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details)

□□□□

□□

CURRENT RATING	10 A IEC 10 A UL
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 REACH Fire and smoke rating I2F3 according to NFF 16101 and NFF 16102 Fire & Smoke RoHS
ENVIRONMENTAL RESISTANCE	Resistant against acid bath Resistant against mineral oil Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz UV resistant, no degradation after 5 years of exposure in natural environment Resistant against gasoline Resistant against oil
TEST CURRENT	7 A CSA 10 A UL 10 A IEC
TEST VOLTAGE	600 V CSA 63 V IEC 600 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Sealing Gland
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	92
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic
SHELL SIZE	14
CABLE DIAMETER - MAX	14 mm

CABLE DIAMETER - MIN	5 mm
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	12
NUMBER OF CAVITY #16	12
SALT SPRAY	500 hour



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

