

Eaton UTS6JC1492SX

Plastic plug, with cable gland backshell, for 12 female contacts, IP68/69K, keying X; UTS6JC1492SX

| | |
|-----------------------------|---|
| | |
| PRODUCT NAME | Eaton Souriau UTS series plastic waterproof IP68/69k connector |
| CATALOG NUMBER | UTS6JC1492SX |
| PRODUCT LENGTH/DEPTH | 71.5 mm |
| PRODUCT HEIGHT | 34.4 mm |
| PRODUCT WIDTH | 34.6 mm |
| PRODUCT WEIGHT | 39.6 g |
| COMPLIANCES | IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) |



| | |
|----------------------------|---|
| CURRENT RATING | 10 A UL 10 A IEC |
| ENVIRONMENTAL CONDITIONS | Fire and smoke rating I2F3 according to NFF 16101 and NFF 16102 RoHS Flammability rating UL94 V0 Fire & Smoke REACH |
| ENVIRONMENTAL RESISTANCE | Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against gasoline Resistant against mineral oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against basic bath Resistant against acid bath Resistant against oil |
| TEST CURRENT | 10 A IEC 7 A CSA 10 A UL |
| TEST VOLTAGE | 63 V IEC 600 V CSA 600 V UL |
| BACKSHELL ANGLE | Straight |
| BACKSHELL TYPE | Sealing Gland |
| CONNECTOR ACCESSORY OPTION | Delivered with connector |
| CONNECTOR ORIENTATION | X |
| CONNECTOR TYPE | Plug |
| CONTACT DELIVERY | Not delivered |
| CONTACT GENDER | Socket (Female) |
| CONTACT TYPE | Crimp |
| COUPLING TYPE | 1/3 Bayonet |
| DEGREE OF PROTECTION | IP68 |
| INSERT MATERIAL | Polyamide |
| LAYOUT | 92 |
| PLUG TYPE | Straight Plug |
| SHELL MATERIAL | Plastic |

| | |
|-----------------------------|----------|
| SHELL SIZE | 14 |
| CABLE DIAMETER - MAX | 14 mm |
| CABLE DIAMETER - MIN | 5 mm |
| MATING CYCLES | 250 |
| OPERATING TEMPERATURE - MAX | 105 °C |
| OPERATING TEMPERATURE - MIN | -40 °C |
| NUMBER OF CONTACTS | 12 |
| NUMBER OF CAVITY #16 | 12 |
| SALT SPRAY | 500 hour |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| : |



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

