

Eaton UTS710D6P32

Plastic jam nut receptacle & hold down clips, without backshell, with 6 male PCB contacts, IP68/69K in unmated conditions; UTS710D6P32

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS710D6P32
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	27 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	10.5 g
COMPLIANCES	IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details) ROHS exemption 6.c CSA-C22.2 No.182.3 (please contact us for more details)

CURRENT RATING	6 A UL 7 A IEC
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 HB RoHS REACH
ENVIRONMENTAL RESISTANCE	Resistant against mineral oil Resistant against oil Resistant against acid bath
	Resistant against gasoline Resistant against basic bath UV resistant, no degradation after 5 years of exposure in natural environment Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz
TEST CURRENT	7 A IEC 6 A UL 6 A CSA
TEST VOLTAGE	32 V IEC 250 V UL 250 V CSA
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	6
SHELL MATERIAL	Plastic
SHELL SIZE	10
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	6
NUMBER OF CAVITY #20	6
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

