

Eaton UTS710D7P

Plastic jam nut receptacle, without backshell, with 7 male PCB contacts, IP68/69K in unmated conditions; UTS710D7P

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS710D7P
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	27 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	10.8 g
COMPLIANCES	UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) ROHS exemption 6.c

CURRENT RATING	7 A IEC 6 A UL
ENVIRONMENTAL CONDITIONS	RoHS Flammability rating UL94 HB REACH
ENVIRONMENTAL RESISTANCE	UV resistant, no degradation after 5 years of exposure in natural environment Resistant against gasoline Resistant against oil Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against acid bath Resistant against mineral oil
TEST CURRENT	7 A IEC 6 A UL 6 A CSA
TEST VOLTAGE	250 V UL 250 V CSA 50 V IEC
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	7
SHELL MATERIAL	Plastic
SHELL SIZE	10
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C

RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	7
NUMBER OF CAVITY #20	7
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

