

Eaton UTS710D7S

Plastic jam nut receptacle, without backshell, with 7 female PCB contacts, IP68/69K in unmated conditions; UTS710D7S

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS710D7S
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	27 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	11.9 g
COMPLIANCES	ROHS exemption 6.c UL 1977 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details)



Powering Business Worldwide

CURRENT RATING	6 A UL 7 A IEC
ENVIRONMENTAL CONDITIONS	RoHS Flammability rating UL94 HB REACH
ENVIRONMENTAL RESISTANCE	Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against oil Resistant against mineral oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against gasoline Resistant against acid bath Resistant against basic bath
TEST CURRENT	6 A CSA 6 A UL 7 A IEC
TEST VOLTAGE	250 V UL 250 V CSA 50 V IEC
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	7
SHELL MATERIAL	Plastic
SHELL SIZE	10
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	7
NUMBER OF CAVITY #20	7
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

