

Eaton UTS710D98PY

Plastic jam nut receptacle, without backshell, with 6 male PCB contacts, IP68/69K in unmated conditions, keying Y; UTS710D98PY

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS710D98PY
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	27 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	10.5 g
COMPLIANCES	IEC 61984 (please contact us for more details) ROHS exemption 6.c CSA-C22.2 No.182.3 (please contact us for more details) UL 1977 (please contact us for more details)

CURRENT RATING	7 A IEC 6 A UL
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 HB RoHS REACH
ENVIRONMENTAL RESISTANCE	Resistant against acid bath
	Resistant against gasoline
	Resistant against basic bath
	Resistant against mineral oil
	Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz UV resistant, no degradation after 5 years of exposure in natural environment Resistant against oil
TEST CURRENT	6 A CSA 6 A UL 7 A IEC
TEST VOLTAGE	50 V IEC 250 V UL 250 V CSA
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	98
SHELL MATERIAL	Plastic
SHELL SIZE	10
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	6
NUMBER OF CAVITY #20	6
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

