

Eaton UTS710D98SZ

Plastic jam nut receptacle, without backshell, with 6 female PCB contacts, IP68/69K in unmated conditions, keying Z; UTS710D98SZ

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS710D98SZ
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	27 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	11.5 g
COMPLIANCES	IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details) ROHS exemption 6.c CSA-C22.2 No.182.3 (please contact us for more details)

CURRENT RATING	7 A IEC 6 A UL
ENVIRONMENTAL CONDITIONS	RoHS REACH Flammability rating UL94 HB
ENVIRONMENTAL RESISTANCE	Resistant against acid bath
	Resistant against oil Resistant against gasoline Resistant against mineral oil
	UV resistant, no degradation after 5 years of exposure in natural environment
	Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz
TEST CURRENT	6 A UL 6 A CSA 7 A IEC
TEST VOLTAGE	50 V IEC 250 V CSA 250 V UL
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	Z
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	98
SHELL MATERIAL	Plastic
SHELL SIZE	10
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	6
NUMBER OF CAVITY #20	6
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

