

Eaton UTS710E98PZ

Plastic jam nut receptacle, without backshell, with 6 male solder contacts, IP68/69K in unmated conditions, keying Z; UTS710E98PZ

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS710E98PZ
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	27 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	10.2 g
COMPLIANCES	UL 1977 (please contact us for more details) ROHS exemption 6.c CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details)

CURRENT RATING	7 A IEC 6 A UL
ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 HB RoHS
ENVIRONMENTAL RESISTANCE	Resistant against gasoline Resistant against acid bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against mineral oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against basic bath Resistant against oil
TEST CURRENT	7 A IEC 6 A CSA 6 A UL
TEST VOLTAGE	250 V CSA 250 V UL 50 V IEC
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	Z
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	98
SHELL MATERIAL	Plastic
SHELL SIZE	10
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	6
NUMBER OF CAVITY #20	6
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: