



## Eaton UTS710E98SX

Plastic jam nut receptacle, without backshell, with 6 female solder contacts, IP68/69K in unmated conditions, keying X; UTS710E98SX

□□□□

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS710E98SX
<b>PRODUCT LENGTH/DEPTH</b>	25.3 mm
<b>PRODUCT HEIGHT</b>	27 mm
<b>PRODUCT WIDTH</b>	27 mm
<b>PRODUCT WEIGHT</b>	11 g
<b>COMPLIANCES</b>	UL 1977 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details) ROHS exemption 6.c

□□□□

□□

<b>CURRENT RATING</b>	6 A UL 7 A IEC
<b>ENVIRONMENTAL CONDITIONS</b>	RoHS Flammability rating UL94 HB REACH
<b>ENVIRONMENTAL RESISTANCE</b>	Resistant against acid bath  Resistant against gasoline Resistant against mineral oil Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against oil Resistant against basic bath UV resistant, no degradation after 5 years of exposure in natural environment
<b>TEST CURRENT</b>	6 A CSA 6 A UL 7 A IEC
<b>TEST VOLTAGE</b>	250 V UL 50 V IEC 250 V CSA
<b>CONNECTOR ACCESSORY OPTION</b>	Not delivered, to be ordered separately
<b>CONNECTOR ORIENTATION</b>	X
<b>CONNECTOR TYPE</b>	Receptacle
<b>CONTACT DELIVERY</b>	Loaded
<b>CONTACT GENDER</b>	Socket (Female)
<b>CONTACT PLATING</b>	Gold
<b>CONTACT TYPE</b>	Solder Cup
<b>COUPLING TYPE</b>	1/3 Bayonet
<b>DEGREE OF PROTECTION</b>	IP68
<b>INSERT MATERIAL</b>	Neoprene
<b>LAYOUT</b>	98
<b>SHELL MATERIAL</b>	Plastic
<b>SHELL SIZE</b>	10
<b>MATING CYCLES</b>	250
<b>OPERATING TEMPERATURE - MAX</b>	105 °C
<b>OPERATING TEMPERATURE - MIN</b>	-40 °C
<b>RECEPTACLE TYPE</b>	Jam Nut Receptacle
<b>NUMBER OF CONTACTS</b>	6

NUMBER OF CAVITY #20	6
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000  
Eaton House  
30 Pembroke Road  
Dublin 4, 0000  
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

